

LESLEY PLUS 6510

Versatile glove for technical interventions. This model excels in flexibility, sensitivity and high protection against mechanical risks.

Colour: Lime Green 
LESLEY PLUS Evo 6510

UPPER MATERIAL:

- **Back:** Durable elastic fabric, color Lime Green.
- **Palm:** Synthetic leather.

REINFORCEMENT:

- Reinforcement of the most exposed areas in the palm – Kevlar® / PA with FR coating and foam padding.
- Reinforcement between thumb and index finger made of Kevlar® / PA with FR coating covers the side seams, increases the life of the glove thanks to high abrasion resistance.
- Anti-slip reinforcements on the fingertips in the palm.
- Protection of the knuckles on the back of the hand against abrasion and impact – Kevlar®/PA with FR coating and foam padding.
- Finger reinforcement on the back of the hand – synthetic leather.

LINING:

- Palm: Para-aramid / PES / Fibreglass knitted lining – high cut resistance.

CUFF:

- **Evo:** Elastic cuff with inner wristband preventing ingress of dirt.



LESLEY PLUS



STANDARDS:

- EN 388
- EN ISO 21420
- EN 407

LESLEY PLUS 6510

OTHER INFORMATION:

- High resistance to mechanical risks.
- Breathability, sensitivity, flexibility and high strength.
- Comfortable cut.
- Anatomically articulated reinforcements in the palm.
- The wrist part is tightened with an elastic band.
- Reflective element.
- Contrast stitching.
- Plastic ring and textile loop for hanging the glove on the carabiner.

Measurement type:	Results before washing	Results after washing
Abrasion resistance	4	4
Blade cut resistance (palm part)	5 / TDM Level D	X / TDM Level D
Tear resistance	4	4
Puncture resistance	4	4
Burning behaviour	-	-
Convection heat resistance	-	-
Radiant heat resistance	-	-
Contact heat resistance	2	2
Dexterity	5	5

SIZE ASSORTMENT

 cm	12,7-15,2	15,2-16,5	16,5 - 19	19 - 21,6	21,6 - 24,2	24,2 - 26,7	26,7 - 29,2	29,2 - 30,4	30,4-32,9
size	5 (XXS)	6 (XS)	7 (S)	8 (M)	9 (L)	10 (XL)	11 (2XL)	12 (3XL)	13 (4XL)

CARE & MAINTENANCE:

Choose a more ecological short washing program at 40 °C.



PROCEDURE: Remove coarse dirt after each use. Before washing, fasten the Velcro fasteners and remove the snaps. Use a liquid detergent. Wash on a short programme.

TO MAKE THE GLOVE FIT BETTER: Shape the glove several times after washing and during drying. Do not dry in direct sunlight or heat sources, do not use a tumble dryer.

Store the gloves in a dry environment.

For more about Washing & Maintenance, visit:

www.holik.com > Technologies > Care&Maintenance



Co-funded by
the European Union



Holik International, s.r.o.

Za Dvorem 612, Štípa, 763 14 Zlín

Tel.: +420 577 125 500

E-mail: info@holik-international.cz

Instagram: [holik_international](https://www.instagram.com/holik_international)

Facebook: [holikinternational](https://www.facebook.com/holikinternational)

Web: www.holik-international.cz

Holik GmbH

Lise-Meitner-Straße 1-13

D-42119 Wuppertal

Tel.: +49 (0) 202 786 6278

Mob.: +49 170 788 8432

E-mail: mail@holik-gmbh.de

Web: www.holik.com



9/2026 CE 1023